

Product data sheet

Specifications



Changeover relay extension ERL 10A 2P Uc 12VAC Ue 250VAC

15542

⚠ Discontinued on: Feb 11, 2019

⚠ Discontinued

Main

Range Of Product	Multi9
Product Name	Multi9 ERL
Product Or Component Type	Extension for changeover relay
Device Short Name	ERL
Device Application	Extension for changeover relay
Signal Contacts Composition	1 C/O + 1 NO
[Uc] Control Circuit Voltage	12 V AC 50/60 Hz

Complementary

[Ie] Rated Operational Current	10 A at 230 V AC (cos Phi = 1)
[Ui] Rated Insulation Voltage	250 V AC
Supply Holding Power	8 VA
Supply Inrush Power	8 VA
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	2
Electrical Durability	AC-21: 100000 cycles
Connections - Terminals	Tunnel type terminals 0.5...6 mm ² Connection by clip

Environment

Standards	NF C 45-250 IEC 255
-----------	------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	1.8 cm
Package 1 Length	7.3 cm
Package 1 Weight	0.117 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------