



### Main

Range	PowerLogic
Device short name	CH
Product or component type	Hour counter
Range compatibility	Prisma P door Prisma G door
Type of measurement	Operating time
Display type	Electromechanical 7 digit(s), number of decimal = 2

### Complementary

Reset	Without
[Us] rated supply voltage	12...36 V DC
Power consumption in VA	0.02 VA at 12 V 0.3 VA at 36 V
Mounting support	Front face

### Environment

IP degree of protection	Front face: IP65
Width	48 mm
Height	48 mm
Depth	39 mm

### Offer Sustainability

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------