



### Main

Range of product	Acti 9
Product name	Acti 9 THP
Device short name	THP1
Product or component type	Programmable thermostat
Colour tint	White (RAL 9003)
Provided equipment	Supplied with non-adjustable ambient temperature probe

### Complementary

Power consumption in VA	1 VA
Number of zones	1
Control type	Push-button Remote contact
Operating mode	Above freezing : 6 °C Comfort : 5...30 °C Reduced : 5...26 °C
Cycle duration	24 hours 7 days
Measurement accuracy	+/- 0.2 °C
Maximum number of switchings	42
Minimum interval duration	1 min
Status LED	1 indicator light color: green for above freezing operating mode 1 indicator light color: red for make position of the output contacts 1 indicator light color: yellow for automatic operating mode 1 indicator light color: yellow for comfort operating mode 1 indicator light color: yellow for reduced operating mode
Backup time	6 years time and program saving
Display type	LCD
Information displayed	Day Hour Minutes

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - terminals	Screw terminals <= 4 mm <sup>2</sup>
9 mm pitches	10
Height	81 mm
Width	90 mm
Depth	65 mm
Compatibility code	THP1

## Environment

IP degree of protection	IP20
-------------------------	------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------