

Product data sheet

Characteristics

16017
cam ammeter switch CMA - 3L-N - 90° - 20 A - for
Ø 22.3 mm



Main

Range of product	PowerLogic
Product or component type	Selector switch
Device short name	CMA
Device application	Ammeter selector

Complementary

[Ie] rated operational current	20 A
Mounting mode	Flush-mounted
Mounting support	Front face
Height	48 mm
Width	48 mm
Depth	69 mm
Mechanical durability	2000000 cycles
Electrical durability	100000 cycles

Environment

Standards	IEC 60947-3
Ambient air temperature for operation	-25...50 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------