



Main

Range of product	DuoLine
Range	DuoLine
Product name	DuoLine BP'cl'ic
Product or component type	Push-button
Device short name	BP'cl'ic
Standards	IEC 60669-1 IEC 60947-5-1
Product certifications	NF

Complementary

Contacts type and composition	1 NO
[Ie] rated operational current	20 A
[Ue] rated operational voltage	250 V AC
Control type	1 push-button grey
Light source	LED
Cap/Operator or lens colour	Green
Bulb lifespan	100000 h
Signalling circuit voltage	AC : 110...230 V 50/60 Hz
Power consumption in W	0.3 W
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside : Bar'cl'ic Upside : ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical durability	AC-22 : 30000 cycles AC 50/60 Hz
Connections - terminals	Staggered tunnel terminal 2 cable(s) 5 mm ² flexible with Staggered tunnel terminal 2 cable(s) 5 mm ² flexible without Staggered tunnel terminal 2 cable(s) 5 mm ² rigid with Staggered tunnel terminal 2 cable(s) 5 mm ² rigid without

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty period	18 months
-----------------	-----------
