



Main

Product or component type	Cartridge
Device short name	C1 Neutral-350
Surge arrester type	Electrical distribution network

Complementary

Surge arrester class type	Type 1
Surge arrester technology	Spark gap
Earthing system	TN TT
[Ue] rated operational voltage	230 V AC 50 Hz
Nominal discharge current	20 kA
[Uc] maximum continuous operating voltage	350 V
[Up] voltage protection level	1.5 kV type 1
[If] follow current	0.1 kA
Mounting mode	Plug-in
Mounting support	Into SPD module
9 mm pitches	4
Height	50 mm
Width	36 mm
Depth	57 mm
Colour	Anthracite grey (RAL 7016)
Material	PBT (polybutylene terephthalate)
Response time	< 100 ns

Environment

Standards	EN 61643-11 IEC 61643-1
Product certifications	KEMA-KEUR
IP degree of protection	Front face : IP20
Relative humidity	5...90 %
Operating altitude	0...2000 m

Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
