

# Product data sheet

Specifications



## Acti9 - IH clic - mechanical time switch - 24 h - 150 h memory

16654

### Main

Range Of Product	DuoLine
Product Name	DuoLine IH' clic
Device Short Name	IH' clic
Product Or Component Type	Mechanical time switch
Number Of Channels	1
Function Available	Manual time changeover

### Complementary

Device Application	Residential
Load Type	Parallel-corrected fluorescent tube 5 x 58 W 4.7 µF Parallel-corrected fluorescent tube 7 x 40 W 7 µF Parallel-corrected fluorescent tube 2 x 100 W 18 µF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W
Cycle Duration	24 h
Maximum Number Of Switchings	48 on - 48 off
Minimum Interval Duration	15 min
Type Of Setting	Manual time changeover
Measurement Accuracy	+/- 1 s/day
Power Consumption In W	0.5 W
Maximum Switching Current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] Rated Operational Voltage	230...240 V AC at 50...60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Backup Time	150 h time and program saving
Mounting Support	DIN rail
9 Mm Pitches	2
Colour Tint	White (RAL 9003)
Connections - Terminals	Screw terminals
Width	18 mm
Net Weight	0.095 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Ambient Air Temperature For Operation	-10...50 °C
Ip Degree Of Protection	Terminals: IP20 B

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.100 cm
Package 1 Width	7.000 cm
Package 1 Length	9.900 cm
Package 1 Weight	88.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7.600 cm
Package 2 Width	10.500 cm
Package 2 Length	22.000 cm
Package 2 Weight	927.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	110
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	10.721 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>