

Product data sheet

Specifications



Thorsman - nail clip - TC 14...20 mm - 2/35/18 - light grey - set of 100

2052033

Main

Range	Thorsman
Range Of Product	Thorsman
Product Or Component Type	Nail clip
Device Short Name	TC
Device Application	Installation of round cable
Cable Type	Round cable 14...20 mm
Type Of Installation	Indoor
Provided Equipment	Nail
Nail Diameter	2 mm
Length	35 mm
Embedding Depth	18 mm

Complementary

Colour Tint	Light grey (NCS 2502-Y)
Material	Clip: PP (polypropylene) Nail: electroplated hardened steel
Ambient Air Temperature For Operation	-40...80 °C
Atmospheric-Corrosivity Category	C2

Environment

Environmental Characteristic	Impact resistant UV resistant
Quantity Per Set	Set of 100
Net Weight	0.00231 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.200 cm
Package 1 Width	1.800 cm
Package 1 Length	3.500 cm
Package 1 Weight	2.300 g
Unit Type Of Package 2	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	84000
Package 2 Height	92.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	234.600 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations