

# Product data sheet

Specifications



## Thorsman - nail clip - TC 22...26 mm - 2.5/45/21 - white - set of 50

2070001

### Main

Range	Thorsman
Range Of Product	Thorsman
Product Or Component Type	Nail clip
Device Short Name	TC
Device Application	Installation of round cable
Cable Type	Round cable 22...26 mm
Type Of Installation	Indoor
Provided Equipment	Nail
Nail Diameter	2.5 mm
Length	45 mm
Embedding Depth	21 mm

### Complementary

Colour Tint	White (NCS 0500)
Material	Clip: PP (polypropylene) Nail: electroplated hardened steel
Atmospheric-Corrosivity Category	C2
Ambient Air Temperature For Operation	-40...80 °C

### Environment

Environmental Characteristic	Impact resistant UV resistant
Quantity Per Set	Set of 50
Net Weight	0.0043 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	2.45 cm
Package 1 Length	3.1 cm
Package 1 Weight	4.96 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	50
Package 2 Height	8.8 cm
Package 2 Width	9.6 cm
Package 2 Length	13.4 cm
Package 2 Weight	248 g
Unit Type Of Package 3	BB2
Number Of Units In Package 3	500
Package 3 Height	13 cm
Package 3 Width	19 cm
Package 3 Length	45.4 cm
Package 3 Weight	2.54 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations