



### Main

Range of product	Multi 9
Product or component type	Shunt trip release
Device short name	MX
[Uc] control circuit voltage	12...24 V AC 50/60 Hz 12...24 V DC
9 mm pitches	2
Product compatibility	C60 IDPN C120 ID DPN C60CTRL N40

### Complementary

Range compatibility	Multi 9: Multi 9 N40 Multi 9: Multi 9 ID Multi 9: Multi 9 C60 C60CTRL
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm 73.5 mm
Product weight	0.06 kg
Connections - terminals	Clamp terminal 2 cable(s) 1.5 mm <sup>2</sup> flexible Clamp terminal 1 cable(s) 0.5...2.5 mm <sup>2</sup> rigid Clamp terminal 2 cable(s) 1.5 mm <sup>2</sup> flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.m

## Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA ASTA KEMA LCIE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## 26478 is replaced by:



### electrical auxiliaries M9A26478

Multi 9 - shunt trip release - MX - 12/24 V AC - 12/24 V DC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017