



Main

Range of product	Multi 9
Product or component type	Fault contact
Device short name	SD
Signal contacts composition	1 C/O
[In] rated current	6 A at 220...240 V AC - 50/60 Hz 1 A at 130 V DC 1.5 A at 60 V DC 2 A at 48 V DC 3 A at 277 V AC - 50/60 Hz 6 A at 12...24 V DC
9 mm pitches	1

Complementary

Range compatibility	Multi 9 C60H-DC Multi 9 C60 Acti 9 iSW-NA
Mounting mode	Fixed
Mounting support	DIN rail
Height	85 mm
Width	9 mm
Depth	73.5 mm
Connections - terminals	Pad terminal 1 cable(s) 2.5 mm ² rigid Pad terminal 2 cable(s) 1.5 mm ² rigid
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA ASTA KEMA LCIE
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1

Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------

26928 is replaced by:



electrical auxiliaries M9A26927

Multi 9 - fault contact - 1 SD - 240/415 V AC - 24/130 V DC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017