



### Main

Range of product	Multi 9
Product or component type	Double OC or fault contact
Device short name	OF and OF or OF and SD
Signal contacts composition	2 C/O
[In] rated current	1 A at 130 V DC 2 A at 48 V DC 6 A at 24 V DC 3 A at 415 V AC - 50/60 Hz 6 A at 240 V AC - 50/60 Hz
9 mm pitches	1

### Complementary

Range compatibility	Multi 9 C60 Acti 9 iSW-NA Multi 9 C60CTRL Acti 9 DPN Vigi Acti 9 RCCB-ID
Mounting mode	Fixed
Mounting support	DIN rail
Height	84 mm
Width	9 mm
Depth	73 mm
Connections - terminals	Clamp terminal 2 cable(s) 1.5 mm <sup>2</sup> flexible Clamp terminal 2 cable(s) 1.5 mm <sup>2</sup> rigid Clamp terminal 1 cable(s) 0.5...2.5 mm <sup>2</sup> rigid Clamp terminal 1 cable(s) 0.5...2.5 mm <sup>2</sup> flexible
Wire stripping length	9 mm
Tightening torque	1 N.m

### Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA ASTA KEMA LCIE

IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Pollution degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

### Contractual warranty

Warranty period	18 months
-----------------	-----------

### 26929 may be replaced by any of the following products:



#### electrical auxiliaries A9A26929

Acti 9 - Auxiliary contact iOF/SD+OF - 2OC - AC/DC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2011



#### electrical auxiliaries M9A26929

Multi 9 - double OC or fault contact - 1 OF+SD/OF - 240/415 V AC - 24/130 V DC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 January 2017