

Product data sheet

Specifications



MN undervoltage release, Compact NS80H-MA, Compact NSC100N, 380 VAC to 415 VAC 50 Hz

28083

⚠ Discontinued on: Oct 10, 2020

⚠ Discontinued

Main

Range	ComPact
Range Of Product	NS80H-MA NSE75...100 NSA125...160 NSC100 NG160NA NG160
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Undervoltage release
[Uc] Control Circuit Voltage	380...415 V AC 50/60 Hz
Range Compatibility	ComPact ComPact NS ComPact Compact NSC ComPact Compact NSE ComPact Compact NG

Complementary

Operating Threshold	0.35...0.7 Un opening 0.85 Un closing
Response Time	< 50 ms
Supply Holding Power	< 5 VA
Auxiliary Connection Terminal	Screw terminal 0...1.5 mm²

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
