



Main

Device short name	Motor mechanism modules with SDE adapter
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	Compact - Compact NS Compact - Compact NSF
[In] rated current	100 A 160 A
[Uc] control circuit voltage	110...130 V AC 50/60 Hz

Complementary

Control type	Standard
Control signal type	Impulse Maintained
Response time	< 600 ms - during open time < 80 ms - during close time
Power consumption in VA	<= 500 VA - during close time <= 500 VA - during open time
Provided equipment	SDE adaptor

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications