

Product data sheet

Specifications



motor-mechanism Compact MT400 - 220..240 V AC

32641

❗ Discontinued

Main

Device Short Name	Motor mechanism modules with SDE adapter
Product Or Component Type	Motor mechanism
Device Application	Automatic spring charging
Range Compatibility	ComPact ComPact NS circuit breaker
Control Type	Standard
[Uc] Control Circuit Voltage	208...277 V AC 60 Hz 220...240 V AC 50/60 Hz
Circuit Breaker Frame Rated Current	400 A

Complementary

Control Signal Type	Maintained Impulse
Maximum Power Consumption In Va	500 VA close 500 VA open
Provided Equipment	SDE adaptor

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications