



33652 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

### Main

Device short name	OF
Product or component type	Auxiliary contact
Range compatibility	Compact Compact NS1600b...3200 Compact Compact NS630b...1600
Offer type	C5 C4
Signal contacts composition	1 NO/NC

### Complementary

Auxiliary contacts type	Standard
Mounting mode	Fixed
[I <sub>th</sub> ] conventional free air thermal current	6 A
[I <sub>e</sub> ] rated operational current	Utilisation category AC-12 : 6 A network: AC 50/60 Hz at 110 V Utilisation category AC-12 : 6 A network: AC 50/60 Hz at 220/240 V Utilisation category AC-12 : 6 A network: AC 50/60 Hz at 24 V Utilisation category AC-12 : 6 A network: AC 50/60 Hz at 380/440 V Utilisation category AC-12 : 6 A network: AC 50/60 Hz at 48 V Utilisation category AC-12 : 6 A network: AC 50/60 Hz at 480 V Utilisation category AC-12 : 6 A network: AC 50/60 Hz at 660/690 V Utilisation category AC-15 : 0.1 A network: AC 50/60 Hz at 660/690 V Utilisation category AC-15 : 1.5 A network: AC 50/60 Hz at 480 V Utilisation category AC-15 : 2 A network: AC 50/60 Hz at 380/440 V Utilisation category AC-15 : 4 A network: AC 50/60 Hz at 220/240 V Utilisation category AC-15 : 5 A network: AC 50/60 Hz at 110 V Utilisation category AC-15 : 6 A network: AC 50/60 Hz at 24 V Utilisation category AC-15 : 6 A network: AC 50/60 Hz at 48 V Utilisation category DC-12 : 0.3 A network: DC at 250 V Utilisation category DC-12 : 0.6 A network: DC at 110 V Utilisation category DC-12 : 2.5 A network: DC at 48 V Utilisation category DC-12 : 6 A network: DC at 24 V Utilisation category DC-14 : 0.03 A network: DC at 250 V Utilisation category DC-14 : 0.05 A network: DC at 110 V Utilisation category DC-14 : 0.2 A network: DC at 48 V Utilisation category DC-14 : 1 A network: DC at 24 V
Minimum load	100 mA at 24 V

### Contractual warranty

Warranty period	18 months
-----------------	-----------