



Main

Device short name	Motor mechanism module
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	Compact - Compact NS630b...1600
[In] rated current	1600 A 1000 A 1250 A 800 A 630 A
[Uc] control circuit voltage	380...415 V AC 50/60 Hz

Complementary

Control type	Standard
Control signal type	Maintained Impulse
Mounting mode	Fixed
Response time	< 600 ms - during open time < 80 ms - during close time
Power consumption in VA	<= 500 VA

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications