

Product data sheet

Specifications



Polinorma - 90° external riser with cover - 60x300 mm - grey

4316730

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Polinorma
Product Or Component Type	External riser
Provided Equipment	Cover
Colour	Grey (RAL 7030)

Complementary

Operating Angle	90 °
Direction Change Type	Vertical
Inner Radius	443 mm
Material	PVC (polyvinyl chloride)
Height	60 mm
Width	300 mm

Environment

Flame Retardance	V0
Standards	EN 60695-11-10 UNE 23727 IEC 61537
Ambient Air Temperature For Operation	-20...60 °C
Ik Degree Of Protection	IK10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	2.4 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations