



### Main

Device short name	Gear motor MCH
Product or component type	Gear motor mechanism MCH
Device application	Automatic spring charging
Range compatibility	Masterpact NT circuit breaker
[Uc] control circuit voltage	100...130 V AC 50/60 Hz

### Complementary

Control type	Motor mechanism
Mounting mode	Fixed
Maximum charging time	3 s
Maximum power consumption in VA	180 VA

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------