



Main

Range of product	Masterpact NW
Range	Masterpact
Device short name	Gear motor MCH
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	Masterpact - Masterpact NW circuit breaker Easypact - EasyPact MVS circuit breaker
[Uc] control circuit voltage	100/125 V DC

Complementary

Control type	Motor mechanism
Charging time	≤ 4 s
Maximum operating frequency	≤ 3 cycles per minute
Threshold tripping voltage	0.85...1.1 Un
Power consumption in VA	180 W
Accessory / separate part category	Spare parts Masterpact NW

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications