



Main

Device short name	EF contact
Product or component type	Auxiliary contact
Device application	Control
Range compatibility	Masterpact - Masterpact NW
Signal contacts composition	1 NO/NC

Complementary

Auxiliary contacts type	Low level
Auxiliary contacts operation	Connected position
Mounting mode	Drawout
[Ie] rated operational current	DC-12 : 0.3 A DC 250 V AC-12 : 5 A AC 50/60 Hz 240 V DC-12 : 0.8 A DC 125 V DC-12 : 2.5 A DC 24/48 V AC-12 : 5 A AC 50/60 Hz 380 V AC-12 : 5 A AC 50/60 Hz 240/380 V
Minimum load	2 mA at 15 V

Contractual warranty

Warranty period	18 months
-----------------	-----------