

# Product data sheet

Specifications



## Thorsman - TEK-UH100 - trunking base pre-punched - 52 mm - white - 2.55 m

5522010

### Main

Range Of Product	Thorsman
Product Name	Thorsman TEK
Product Or Component Type	Installation trunking
Cabling Installation System	Trunking
Colour Tint	White (NCS 0401-Y62R)
Quantity Per Set	10 m

### Complementary

Compartment Partitioning	1 compartment
Trunking Dimension	100 x 52 mm
Trunking Material	Plastic
Front Opening Size	80 mm
Fixing Mode	By brackets By screws
Material	PVC (polyvinyl chloride)
Type Of Side Profile	C-profile
Length	2500 mm
Height	100 mm
Width	52 mm

### Environment

Quality Labels	CE
Standards	EN 50085-1:1997/A1 EN 50085-1:1998 KEMA 55A:1984 SS 424 10 02:1993
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.400 cm
Package 1 Width	9.600 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	255.000 cm
Package 1 Weight	1.700 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	96
Package 2 Height	50.000 cm
Package 2 Width	120.000 cm
Package 2 Length	260.000 cm
Package 2 Weight	213.684 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations