



Main

Range of product	Thorsman
Product name	Thorsman TEK
Product or component type	Installation trunking
Cabling installation system	Trunking
Colour tint	White NCS 0401-Y62R
Quantity per set	10 m
Market segment	Small commercial

Complementary

Compartment partitioning	1 compartment
Trunking dimension	123 x 72 mm
Trunking material	Plastic
Front opening size	80 mm
Fixing mode	By brackets By screws
Material	PVC (polyvinyl chloride)
Type of side profile	C-profile
Length	2500 mm
Height	123 mm
Width	72 mm

Environment

Quality labels	CE
Standards	EN 50085-1 1997/A1 EN 50085-1 1998 KEMA 55A 1984 SS 424 10 02 1993
Ambient air temperature for operation	-20...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental health and issues	Cadmium free Lead free
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1826 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------