

# Product data sheet

Specifications



## Thorsman - POL-OM - pole - one installation box - free-standing - natural

5860544

! Discontinued

! Discontinued on: Sep 30, 2020

! End-of-service on: Oct 26, 2020

### Main

|                                |                                  |
|--------------------------------|----------------------------------|
| Range                          | Thorsman                         |
| Product Name                   | Thorsman POL                     |
| Product Or Component Type      | Pole                             |
| Type Of Pole                   | One installation box             |
| Device Presentation            | Pre-wired                        |
| Provided Equipment             | 2000 mm flexible conduit         |
| Colour Tint                    | Natural                          |
| Number Of Power Socket Outlets | 8 x 16 A - side earth            |
| Number Of Data Socket Outlets  | 2 x RJ45 Cat.6<br>2 x RJ45 blind |
| Quantity Per Set               | Set of 1                         |

### Complementary

|                          |               |
|--------------------------|---------------|
| Pole/Post Surface Finish | Anodized      |
| Pole Fixing Mode         | Free-standing |
| Front Opening Size       | 80 mm         |
| Material                 | Aluminium     |
| Length                   | 89 mm         |
| Height                   | 2173 mm       |
| Width                    | 100 mm        |
| Cover Type               | closed cover  |

### Environment

|                                       |                                       |
|---------------------------------------|---------------------------------------|
| Standards                             | SS 424 10 32 : 1989<br>PrEN 50085-2-4 |
| Ambient Air Temperature For Operation | -25...60 °C                           |
| Ip Degree Of Protection               | IP30                                  |

### Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |         |
|------------------|---------|
| Package 1 Height | 13 cm   |
| Package 1 Width  | 16 cm   |
| Package 1 Length | 22.5 cm |
| Package 1 Weight | 6.6 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

|                   |  |
|-------------------|--|
| Eu Rohs Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--|

|                          |   |
|--------------------------|---|
| Environmental Disclosure | <a href="#">Product Environmental Profile</a> |
|--------------------------|---|

|                     |  |
|---------------------|--|
| Circularity Profile | No need of specific recycling operations |
|---------------------|--|