

Product data sheet

Specifications



Thorsman - POL-T20 - two-sided - tension-mounted - natural

5863602

 **Discontinued on:** Jun 30, 2022

 **Discontinued**

Main

Range	Thorsman
Product Name	Thorsman POL
Product Or Component Type	Pole
Shape	Oval
Type Of Pole	Two-sided
Device Presentation	Empty
Provided Equipment	400 mm adjustable ceiling fixing
Colour Tint	Natural
Quantity Per Set	Set of 1
Adjustment	Adjustable in height: 400 mm
Useful Cross Section	10942 mm²
Compartment Partitioning	2 compartments

Complementary

Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Tension-mounted
Front Opening Size	80 mm
Material	Aluminium anodized
Length	117 mm
Height	2870...3270 mm
Width	120 mm
Cover Type	2 closed cover cover 80 mm in aluminium anodized

Environment

Standards	PrEN 50085-2-4 SS 424 10 32 : 1989
Ambient Air Temperature For Operation	-25...40 °C
Ip Degree Of Protection	IP30

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	12.41 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations