

Product data sheet

Specifications



Thorsman - CYB-PS - socket outlet - double slave - 37° - white RAL 9010

5940011

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Thorsman
Product Name	Thorsman CYB
Product Or Component Type	Socket-outlet
Device Presentation	Connection kit
Provided Equipment	-
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 1

Complementary

Device Composition	End piece
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	250 V
Number Of Power Socket Outlets	2 x 2P + E with shutters, side earth
Ground Lug Position	37° ground lug
Device Connection	Plug into master or slave outlet
Connections - Terminals	Flat pads for crimped lug
Fixing Mode	Snap-fitted
Material	PC/ABS
Length	94 mm
Height	84 mm
Width	39 mm

Environment

Standards	IEC 60884-1
Ambient Air Temperature For Operation	-20...40 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	99.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations