



### Main

Range of product	Thorsman
Product name	Thorsman CYB
Product or component type	Slave socket-outlet
Device presentation	Connection kit
Provided equipment	3-pole male Wieland GST18 adaptor
Colour tint	White (NCS 0701-G46Y)
Quantity per set	Set of 1

### Complementary

Device composition	Label window End piece Protective cover
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Number of power socket outlets	2 x 2P + E with shutters, side earth
Ground lug position	37° ground lug
Device connection	Plug into slave outlet
Connections - terminals	Flat pads for crimped lug
Fixing mode	Snap-fitted
Material	PC/ABS
Length	140 mm
Height	84 mm
Width	39 mm

### Environment

Standards	IEC 60884-1
Ambient air temperature for operation	-20...40 °C

IP degree of protection	IP20
-------------------------	------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------