



ⓘ Discontinued

65748 has not been replaced. Please contact your customer care center for more information.

### Main

Range of product	VarSet
Device short name	Varset Harmony
Device presentation	Cubicle A4B
Network frequency	50 Hz
Capacitor technology	3P capacitor
Reactive power rating	550 kvar for 400 V AC 50 Hz
Number of steps	11 x 50 kvar
Network rated voltage	400...415 V AC 50 Hz
Network pollution level	Highly polluted ( > 25...< 50 % ) at 400...415 V
[Ui] rated insulation voltage	690 V

### Complementary

Device composition	Circuit-breaker equipment protection Contactor Controller equipment regulation Detuned reactors Incoming circuit-breaker equipment protection Varplus <sup>2</sup> capacitors
Device wiring	Cables
Internal voltage transformer	400/230 V
Capacitor voltage	480 V AC 50 Hz
Tuning order	3.8 - 190 Hz
Capacitance tolerance	- 5 % to 10 %
Rated short-duration power frequency withstand voltage	2.5 kV 50 Hz 1 minute
Maximum permissible voltage	1.1 x Un
[Imp] maximum permanent current	400 V : 1.19 x I1
Colour code	( RAL 9001 )
Height	2000 mm
Width	2150 mm
Depth	600 mm
Product weight	750 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	EN 60439-1 IEC 61921 IEC 60439-1
IP degree of protection	IP31
Ambient air temperature for operation	-5...40 °C
Average ambient air temperature for operation	25 °C ( annual ) 35 °C ( over 24 hours )

## Contractual warranty

Warranty period	18 months
-----------------	-----------