

Product data sheet

Specifications



capacitor bank - Varset Direct Comfort - 400/415V - 20kvar - 50Hz - with CB

65771

⚠ Discontinued on: Dec 31, 2013

⚠ End-of-service on: Jun 23, 2023

⚠ Discontinued

Main

Range Of Product	Varset Direct
Device Short Name	Varset Comfort
Product Or Component Type	Capacitor bank
Device Presentation	Enclosure C1
Network Frequency	50 Hz
Capacitor Technology	3P capacitor
Reactive Power Rating	20 kvar for 400 V AC 50 Hz
Number Of Steps	1 x 20 kvar
Network Rated Voltage	400 V AC 50 Hz 415 V AC 50 Hz
Network Pollution Level	Polluted (15...25 %) at 400 V
[Ui] Rated Insulation Voltage	690 V

Complementary

Device Composition	Circuit-breaker equipment protection Varplus² capacitors
Device Wiring	Cables
Internal Voltage Transformer	400/230 V
Capacitor Voltage	480 V AC, 50 Hz
Capacitance Tolerance	- 5 % to 10 %
Rated Short-Duration Power Frequency Withstand Voltage	2.5 kV 50 Hz 1 minute
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
Colour Code	RAL 9001
Height	450 mm
Width	500 mm
Depth	275 mm
Net Weight	20 kg

Environment

Standards	IEC 60439-1 IEC 61921 EN 60439-1
-----------	--

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP31
Ambient Air Temperature For Operation	-5...40 °C
Average Ambient Air Temperature For Operation	25 °C (annual) 35 °C (over 24 hours)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	45.0 cm
Package 1 Width	50.0 cm
Package 1 Length	27.5 cm
Package 1 Weight	23.0 kg

Contractual warranty

Warranty	18 months
----------	-----------