

# Product data sheet

## Characteristics

# 65786

capacitor bank - Varset Direct Comfort - 400/415V  
- 105kvar - 50Hz



65786 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

### Main

Range of product	Varset Direct
Device short name	Varset Comfort
Device presentation	Enclosure C2
Network frequency	50 Hz
Capacitor technology	3P capacitor
Reactive power rating	105 kvar for 400 V AC 50 Hz
Number of steps	1 x 105 kvar
Network rated voltage	400...415 V AC 50 Hz
Network pollution level	Polluted ( > 15...< 25 % ) at 400...415 V
[Ui] rated insulation voltage	690 V

### Complementary

Device composition	Varplus <sup>2</sup> capacitors
Device wiring	Cables
Internal voltage transformer	400/230 V
Capacitor voltage	480 V AC 50 Hz
Capacitance tolerance	- 5 % to 10 %
Rated short-duration power frequency withstand voltage	2.5 kV 50 Hz 1 minute
Maximum permissible voltage	1.1 x Un 8 hours over 24 hours conforming to IEC 60831
Colour code	( RAL 9001 )
Height	800 mm
Width	500 mm
Depth	275 mm
Product weight	55 kg

### Environment

Standards	EN 60439-1 IEC 60439-1 IEC 61921
IP degree of protection	IP31
Ambient air temperature for operation	-5...40 °C

---

Average ambient air temperature for operation	25 °C ( annual ) 35 °C ( over 24 hours )
---	---

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---