


# Product data sheet

Specifications



## Wibe - wall bracket 11/75 - steel Zinkpox coated white

713207

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

Range	Wibe
Range Of Product	Wibe Cable Ladders
Product Or Component Type	Wall bracket
Device Short Name	11/75
Provided Equipment	Screw M8x 40 + nuts

### Complementary

Accessory / Separate Part Category	Mounting and fixing accessory
Load Bearing Capacity	1 N
Mounting Support	wall
Product Destination	cable ladder
Material With Surface Treatment	Steel, Zinkpox coated white
Corrosion Class	C5-I
Height	135 mm
Width	40 mm
Depth	71 mm
Net Weight	30 kg / set of 100

### Environment

Mounting Location	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards
-------------------	---

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	7.8 cm
Package 1 Length	13.4 cm
Package 1 Weight	240 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations