



Main

Range	Wibe
Range of product	Wibe Cable Ladders
Product or component type	Wall bracket
Device short name	11/25
Provided equipment	Screw M8x 40 + nuts

Complementary

Accessory / separate part category	Mounting and fixing accessory
Load bearing capacity	2.5 N
Mounting support	Wall
Product destination	Cable ladder
Material with surface treatment	Steel, Zinkpox coated white
Corrosion class	C5-I
Height	85 mm
Width	40 mm
Depth	71 mm
Product weight	24 kg / set of 100

Environment

Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards
-------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------