

Product data sheet

Characteristics

714064

Wibe - cable ladder - KHZ-600 - steel Zinkpox coated white - 6 m



Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Cable ladder
Device short name	KHZ
Device application	Industrial application

Complementary

Type of side profile	Closed profile
Type of rung	Round
Mounting location	Indoor Outdoor
Rung spacing	250 mm
Material with surface treatment	Steel, Zinkpox coated white
Corrosion class	C5-I
Height	55 mm
Width	597 mm
Length	6 m
Product weight	360 kg / 100 m

Environment

Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards
Standards	IEC 61537

Contractual warranty

Warranty period	18 months
-----------------	-----------