



### Main

Range	Wibe
Range of product	Wibe Cable Ladders
Device short name	15
Product or component type	90° interior bend

### Complementary

Direction change type	Horizontal
Inner radius	268 mm
Type of side profile	Closed profile
Type of rung	Perforated profile
Product destination	Cable ladder 600 mm width
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Height	55 mm
Width	997 mm
Depth	997 mm
Net weight	440 kg / set of 100

### Environment

Mounting location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants
-------------------	--

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------