

# Product data sheet

Specifications



## Wibe - 90° interior bend 15-200 - steel Zinkpox coated white

716075

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

Range	Wibe
Range Of Product	Wibe Cable Ladders
Device Short Name	15
Product Or Component Type	90° interior bend

### Complementary

Direction Change Type	Horizontal
Inner Radius	268 mm
Type Of Side Profile	Closed profile
Type Of Rung	Perforated profile
Product Destination	Cable ladder 200 mm width
Material With Surface Treatment	Steel, Zinkpox coated white
Corrosion Class	C5-I
Height	55 mm
Width	597 mm
Depth	597 mm
Net Weight	240 kg / set of 100

### Environment

Mounting Location	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards
-------------------	---

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	59 cm
Package 1 Length	61 cm
Package 1 Weight	2.285 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations