


# Product data sheet

Specifications



## Wibe - 90° interior bend 15-400 - steel Zinkpox coated white

716078

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

|                           |                    |
|---------------------------|--------------------|
| Range                     | Wibe               |
| Range Of Product          | Wibe Cable Ladders |
| Device Short Name         | 15                 |
| Product Or Component Type | 90° interior bend  |

### Complementary

|                                 |                             |
|---------------------------------|-----------------------------|
| Direction Change Type           | Horizontal                  |
| Inner Radius                    | 268 mm                      |
| Type Of Side Profile            | Closed profile              |
| Type Of Rung                    | Perforated profile          |
| Product Destination             | Cable ladder 400 mm width   |
| Material With Surface Treatment | Steel, Zinkpox coated white |
| Corrosion Class                 | C5-I                        |
| Height                          | 55 mm                       |
| Width                           | 797 mm                      |
| Depth                           | 797 mm                      |
| Net Weight                      | 340 kg / set of 100         |

### Environment

|                   |   |
|-------------------|---|
| Mounting Location | Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards |
|-------------------|---|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 5.5 cm  |
| Package 1 Width              | 79.7 cm |
| Package 1 Length             | 79.7 cm |
| Package 1 Weight             | 3.4 kg  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |