



### Main

Range	Wibe
Range of product	Wibe Cable Ladders
Product or component type	T-junction
Device short name	16

### Complementary

Inner radius	268 mm
Type of side profile	Closed profile
Type of rung	Perforated profile
Product destination	Cable ladder 400 mm width
Material with surface treatment	Steel hot-dip galvanized
Corrosion class	C3/C4
Length	1197 mm
Height	55 mm
Width	797 mm
Product weight	440 kg / set of 100

### Environment

Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants
-------------------	---

### Contractual warranty

Warranty period	18 months
-----------------	-----------