



Main

| | |
|---------------------------|--------------------|
| Range | Wibe |
| Range of product | Wibe Cable Ladders |
| Product or component type | T-junction |
| Device short name | 16 |

Complementary

| | |
|---------------------------------|----------------------------|
| Inner radius | 268 mm |
| Type of side profile | Closed profile |
| Type of rung | Perforated profile |
| Product destination | Cable ladder 1000 mm width |
| Material with surface treatment | Steel hot-dip galvanized |
| Corrosion class | C3/C4 |
| Length | 1797 mm |
| Height | 55 mm |
| Width | 1397 mm |
| Product weight | 860 kg / set of 100 |

Environment

| | |
|-------------------|---|
| Mounting location | For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants |
|-------------------|---|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications