



Main

Range	Wibe
Range of product	Wibe Cable Ladders
Product or component type	X-junction
Device short name	17

Complementary

Inner radius	268 mm
Type of side profile	Closed profile
Type of rung	Perforated profile
Product destination	Cable ladder 400 mm width
Material with surface treatment	Steel hot-dip galvanized
Corrosion class	C3/C4
Length	1197 mm
Height	55 mm
Width	1197 mm
Product weight	550 kg / set of 100

Environment

Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants
-------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------