



Main

Range	Wibe
Range of product	Wibe Cable Ladders
Product or component type	X-junction
Device short name	17

Complementary

Inner radius	268 mm
Type of side profile	Closed profile
Type of rung	Perforated profile
Product destination	Cable ladder 500 mm width
Material with surface treatment	Steel Zinkpox coated white
Corrosion class	C5-I
Length	1297 mm
Height	55 mm
Width	1297 mm
Product weight	600 kg / set of 100

Environment

Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards
-------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------