

# Product data sheet

## Characteristics

# 716245

## Wibe - 90° interior bend 55-500 - steel hot-dip galvanized



### Main

Range	Wibe
Range of product	Wibe Cable Ladders
Device short name	55
Product or component type	90° interior bend

### Complementary

Direction change type	Horizontal
Inner radius	268 mm
Type of rung	Perforated profile
Product destination	500 mm width reinforced cable ladder
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Height	150 mm
Width	925 mm
Depth	925 mm
Product weight	680 kg / set of 100

### Environment

Mounting location	For area with high level of environmental corrosion, humidity and airborne pollution, such as industrial and coastal areas, chemical plants
-------------------	---

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.