



### Main

Range	Wibe
Range of product	Wibe Cable Ladders
Product or component type	T-junction
Device short name	56

### Complementary

Inner radius	268 mm
Type of rung	Perforated profile
Product destination	Reinforced cable ladder 500 mm width
Material with surface treatment	Steel Zinkpox coated white
Corrosion class	C5-I
Length	1350 mm
Height	150 mm
Width	925 mm
Product weight	940 kg / set of 100

### Environment

Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards
-------------------	--

### Contractual warranty

Warranty period	18 months
-----------------	-----------