



### Main

Range	Wibe
Range of product	Wibe Cable Ladders
Product or component type	T-junction
Device short name	56

### Complementary

Inner radius	268 mm
Type of side profile	Closed profile
Type of rung	Perforated profile
Product destination	Reinforced cable ladder 600 mm width
Material with surface treatment	Steel Zinkpox coated white
Corrosion class	C5-I
Length	1450 mm
Height	150 mm
Width	1025 mm
Product weight	1010 kg / set of 100

### Environment

Mounting location	For area with almost permanent high levels of humidity and airborne pollution, such as tunnels and dockyards
-------------------	--

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications