



Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Cable ladder
Device short name	KHZP
Device application	Industrial application

Complementary

Type of side profile	Closed profile
Type of rung	Perforated profile
Mounting location	Outdoor Indoor
Rung spacing	250 mm
Material with surface treatment	Steel, hot-dip galvanized
Corrosion class	C3/C4
Height	55 mm
Width	297 mm
Length	6 m
Net weight	290 kg / 100 m

Environment

Mounting location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants
Standards	IEC 61537

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration

REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------