



### Main

Range	Wibe
Range of product	Wibe Cable Ladders
Product or component type	T-junction
Device short name	16

### Complementary

Inner radius	268 mm
Type of side profile	Closed profile
Type of rung	Perforated profile
Product destination	Cable ladder 600 mm width
Material with surface treatment	Stainless steel AISI 316L
Corrosion class	C5-M
Length	1397 mm
Height	55 mm
Width	997 mm
Product weight	600 kg / set of 100

### Environment

Mounting location	For area with almost permanent high levels of humidity, airborne pollution and salt, such as purify-ing plants and offshore
-------------------	---

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications