



### Main

|                           |                    |
|---------------------------|--------------------|
| Range                     | Wibe               |
| Range of product          | Wibe Cable Ladders |
| Product or component type | X-junction         |
| Device short name         | 17                 |

### Complementary

|                                 |                           |
|---------------------------------|---------------------------|
| Inner radius                    | 268 mm                    |
| Type of side profile            | Closed profile            |
| Type of rung                    | Perforated profile        |
| Product destination             | Cable ladder 400 mm width |
| Material with surface treatment | Stainless steel AISI 316L |
| Corrosion class                 | C5-M                      |
| Length                          | 1197 mm                   |
| Height                          | 55 mm                     |
| Width                           | 1197 mm                   |
| Product weight                  | 550 kg / set of 100       |

### Environment

|                   |   |
|-------------------|---|
| Mounting location | For area with almost permanent high levels of humidity, airborne pollution and salt, such as purify-ing plants and offshore |
|-------------------|---|

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications