



## Main

Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	LED lighting : : 100 W Compact fluorescent lamp : : 100 W Motor : : 100 W Relay : : 5 A - 250 V Halogen lamp : : 1000 W - 230 V Incandescent lamps : : 2000 W - 230 V Fluorescent tube : 900 VA
Colour tint	White

## Complementary

Network frequency	50/60 Hz
Input function	Switch External trigger
Output voltage	220...250 V
Output current	10 A
Number of channels	2
Control type	Movement sensor
Function available	Switching, toggling, dimming
Light intensity adjustment	10...2000 lux
Horizontal detection angle	360 °
Detection range	Radius 14000 mm
Device mounting	Flush Surface
Mounting height	2.5 m

## Environment

IP degree of protection	IP52 IP40
-------------------------	--------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1611 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available