



### Main

Range	PratiKa
Product or component type	Interlocked socket
Device short name	Unika socket
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

### Complementary

Mounting mode	Panel-mounted
[In] rated current	16 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	9 h
Protection type	Without protection
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Sleeves: nickel plated brass
Connections - terminals	Captive screws
Maximum cable cross section	10 mm <sup>2</sup>
Maximum cable outer diameter	25 mm
Cable entry	Cable gland
Thread type	Pg 21
Net weight	0.64 kg
Base dimension	103 x 225 mm
Height	225 mm
Width	103 mm
Depth	126 mm

Colour	Grey (RAL 7035)
Voltage colour	Red

## Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 62262
Fire resistance	750 °C conforming to IEC 60695-2-11
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C ( 86400 s ) -25...40 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations