

Product data sheet

Specifications



Unika interlocked socket - 16 A - 3P + N + E - 200...250 V AC - IP65 - wall

83083

⚠ Discontinued on: Jun 30, 2022

⚠ Discontinued

Main

| | |
|---------------------------|--------------------|
| Range | PratiKa |
| Product Or Component Type | Interlocked socket |
| Device Short Name | Unika socket |
| Plug, Socket Category | Low voltage |
| Poles Description | 3P + N + E |
| Network Type | AC |
| Outlet Standard | Industrial |

Complementary

| | |
|--------------------------------|---|
| Mounting Mode | Wall-mounted |
| [In] Rated Current | 16 A |
| [Ue] Rated Operational Voltage | 200...250 V |
| Network Frequency | 50/60 Hz |
| Ground Lug Clockwise Position | 9 h |
| Protection Type | Without protection |
| Plug, Socket Material | Housing: self-extinguishing engineering polymer |
| Contacts Material | Sleeves: nickel plated brass |
| Connections - Terminals | Captive screws |
| Maximum Cable Cross Section | 10 mm² |
| Maximum Cable Outer Diameter | 25 mm |
| Cable Entry | Cable gland |
| Thread Type | Pg 21 |
| Net Weight | 1.04 kg |
| Base Dimension | 103 x 255 mm |
| Height | 255 mm |
| Width | 103 mm |
| Depth | 151 mm |
| Colour | Grey (RAL 7035) |
| Voltage Colour | Blue |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|---------------------------------------|---|
| Standards | IEC 60309-2 IEC 60309-1 |
| Ip Degree Of Protection | IP65 conforming to IEC 60529 |
| Ik Degree Of Protection | IK09 conforming to EN 62262 |
| Fire Resistance | 750 °C conforming to IEC 60695-2-11 |
| Relative Humidity | 50 % at 40 °C 70 % at 30 °C 90 % at 20 °C |
| Ambient Air Temperature For Operation | 35 °C (86400 s) -25...40 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 10.7 cm |
| Package 1 Width | 16.8 cm |
| Package 1 Length | 26.3 cm |
| Package 1 Weight | 929 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|