



Main

Range	PratiKa
Product or component type	Interlocked socket
Device short name	Unika socket
Plug, socket category	Low voltage
Poles description	2P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
[In] rated current	16 A
[Ue] rated operational voltage	200...250 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Protection type	Fuse
Fuse type	Cylindrical
Fuse size	10.3 x 38 mm
Plug, socket material	Self-extinguishing engineering polymer housing :
Contacts material	Nickel plated brass sleeves :
Connections - terminals	Captive screws
Cable cross section	<= 10 mm ²
Cable outer diameter	<= 25 mm
Cable entry	Cable gland
Thread type	Pg 21
Product weight	1.04 kg
Base dimension	103 x 255 mm
Height	255 mm
Width	103 mm
Depth	150 mm
Colour	Grey (RAL 7035)
Voltage colour	Blue

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 62262
Fire resistance	750 °C conforming to IEC 60695-2-11
Relative humidity	50 % (40 °C) 70 % (30 °C) 90 % (20 °C)
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------